

Product Name :
AUTO REFRACTOMETER WITH KERATOMETERs**Product Code :**
NMCBS139032**Description :**

AUTO REFRACTOMETER WITH KERATOMETER We are engaged in offering Auto Refractometer with Keratometer. This equipment is used for quick and accurate keratometry measurement. Equipped SLD and highly sensitive CCD for high measurability of densely cataractous eyes and pseudophakic eyes, this equipment is designed using excellent quality components with latest technology. Features With Auto-tracing feature, operator can adjust the focus and alignment in up and down direction With Auto video taping feature, operator can take measurements automatically once equipment obtains satisfactory focus and alignment With Servo Chin-Rest, operator can adjust height of Chin-rest easily Display is tilt-adjustable Printer has a paper auto-cut feature

Specifications Color screen/Auto test Vertex Distance(vd) 0.0, 12.0, 13.75mm Sphere Power(SPH) -20.00~+20.00D(in case of VD=12mm) Cylinder Power(CYL) 0.00~i ½10.00D(0.12/0.25D Unit) Axis(AX) 1~1800 (10 Unit) Cylinder Form -, +, MIX Pupil Distance(PD) 10~80mm Minimum Pupil Diameter c2.00mm Radius of Curvature 5.0~10.2mm(Increments:0.01mm) Corneal Power 33.00~67.50D(When corner equivalent refractive AUTO REFRACTOMETER WITH KERATOMETER, ENT Equipment exporters, ENT Equipment manufacturers