

Product Name :
Slit Lamp Zoom**Product Code :**
OPHTH2010016**Description :**

Zoom Slit Optical Head with Beam Splitter 'C' Mount Slit lamp Zoom Mag with CCD Digital Camera. It also has the features of slit length & width adjustment. This is helpful in all kind of intensity control of illumination i.e low, medium & high.

View Type : Gem Zoom Optical Head with Beam Splitter 'C' Mount & Camera
Magnification: 5x,10x,15x,20x & 25x continuous zoom
Interpupillary Distance : 52mm to 80mm
Camera : CCD Digital Camera

Illumination Section

Slit Width Adjustment : 0 to 12mm without steps
Slit Length Adjustment: 0 to 12mm continuous
Diameter of Diaphragm :12mm, 10mm, 8mm, 5mm, 3mm, 2mm, 1mm and 0.2mm
Angle of Rotation of Slit: 90 Degree
Tilt of Slit (Degree): Horizontal in steps of 0, 5, 10, 15
Vertical in steps (Degree) 0, 5, 10, 15, 20
Filters : Cobalt Blue, Green,
Neutral Density, Heat absorbing
Light Source: Halogen Lamp 12v-50w
Intensity Control of Illumination: Low, Medium and High Slit Lamp Zoom, Ophthalmic Equipments Exporters,
Ophthalmic Equipments Manufacturers

NAUGRA[®]

Medical Hospital Equipments Manufacturers

Website: [SITE](#)