

Product Name :
DRYING OVEN INDUSTRIAL**Product Code :**
NMCBS11002**Description :**

DRYING OVEN INDUSTRIAL Specification:- DRYING OVEN INDUSTRIAL Chamber Size : a) 900 x 600 x 600 (36x24x24") b) 1200 x 900 x 600 (48x36x24") c) 1500 x 900 x 900 (60x36x36") d) 1800 x 1200 x 900 (72x48x36") Optional : i) Timer 0-24 hours. ii) Digital temp. Indicator -cum-Controller. Inner & output chamber : Thick mild steel sheet Make : Ajanta Standard double wall fabrication. Inner chamber backed silver paint finish and exterior finished in hammertone. Heavy duty forced air blowers are provided to constantly circulated hot air to achieve uniform temp. In the whole chamber. Double wall door is mounted on heavy hinges and provided with heavy moulded latch. Temperature is controlled by a thermostat and it can be read on dial type thermometer. Temperature range: 50o C to 250o 2oC to 5oC and equipment is workable on 220 workable on 220V AC 50Hz single phase or 440 volts AC supply. Note: Please ask for the other capacities of your requirement. DRYING OVEN INDUSTRIAL, Heat And Refrigeration System Exporters, Heat And Refrigeration System Manufacturers

NAUGRA[®]**Medical Hospital Equipments Manufacturers**

Website:Medical Hospital Equipments Manufacturers,